Dynabrade Premium Random Orbital Sanding Pads



Dynabrade Sanding Pads <u>Can</u> Make Ask for the a Difference in Finishing Quality! **ORANGE!**

- Engineered for top performance. Actually helps minimize vibration on sanders.
 Perfectly balanced and weight-mated to Dynabrade tools for achieving consistent swirl-free finishes.
- > Designed to last using **premium materials**.



- Exclusive SINGLE-PIECE Hub Design!
- All pads have common 5/16"-24 male thread.
- Fits many brands of sanders!
- 13,000 RPM maximum operating speed.

> Priced competitively.



PSA-Type

 76006
 5" Vacuum

 76007
 5" Non-Vacuum

 76008
 6" Vacuum

 76009
 6" Non-Vacuum

Hook-Face

- 76010 5" Vacuum
- 76011 5" Non-Vacuum
- 76012 6" Vacuum
- 76013 6" Non-Vacuum

Store Counter Display Pack

Each display pack consists of ten pads in a refillable Dynabrade display box. All pads are PSA-Type.

95994	5" Non-Vacuum
95995	5" Vacuum
95996	6" Non-Vacuum
95997	6" Vacuum

See reverse side to read about our Quality!



DYNABRADE AUTOMOTIVE AFTERMARKET

8989 Sheridan Drive • Clarence, New York 14031-1419 Phone: 716-631-0100 • Fax: 716-631-2073



AutoAft@Dynabrade.com

www.DynabradeAuto.com

Dynabrade Premium Pad Facts:



Serious As Serious Gets About Quality...

- Single-piece machined 5/16"-24 external threaded stud. This is the foundation of the pad. We machine the stud to tolerances of .0015" (one and one-half thousands!) Many competitors have pads that are manufactured with a 2-piece design that leads to higher run-out. Fits other companies' sanders too.
- **Top washer** held to .0015" flatness important for balance.
- Fiberglass backing is 100% inspected through a pass-through gauge to insure flatness before assembly.
- The <u>complete hub</u> is assembled and inspected for face run-out before going to foam molding. If the hub runs out – so will the pad!
- <u>Riveting</u> we compress the unit flat; then rivet all 4 rivets simultaneously; other companies will rivet "one at a time" and end up twisting the pad.
- Urethane foam Dynabrade uses a premium custom compounded urethane that will not shrink or curl; this adds to our premium quality.
- PSA material there are many grades of vinyl. We use only high-quality that will not separate from its woven cloth substrate material used for dynamic strength.
- Hook-face material We have top-quality J-Hook facing material. We use nylon, which has the highest temperature rating of all hook materials. Cheaper materials used by others are polyester and polypropylene.
- Our weight and durometer (hardness) are highly controlled; this ensures vibration levels are at their absolute lowest.



DYNABRADE AUTOMOTIVE AFTERMARKET

8989 Sheridan Drive • Clarence, New York 14031-1419 Phone: 716-631-0100 • Fax: 716-631-2073



AutoAft@Dynabrade.com

www.DynabradeAuto.com